

## IntelliPAP®2 AutoAdjust® CPAP System

HCPCS: E0601



FIGURE A



FIGURE B

- PulseDose® Heated Humidification System A truly innovative approach to managing rainout in the patient tubing and mask by providing humidified air to the patient during inhalation and dry air during exhalation
- PureView AutoAdjust® Algorithm - Our most advanced algorithm yet, PureView offers improved sensitivity to a full spectrum of patient events from a simple obstruction to the most complex apnea, providing the most comfortable therapy experience possible based on the patients natural breathing pattern
- Connectivity With Bluetooth® standard on every unit, staying connected with patient therapy has never been so easy The SmartLink® App allows patients to view their therapy results from their smartphone and transmit this data wirelessly for download into SmartLink desktop software

PRODUCTS	Description
DV64D	IntelliPAP 2 AutoAdjust CPAP
DV64D-HH	IntelliPAP 2 AutoAdjust CPAP W/HH

  

SPECIFICATIONS	Description
Auto On/Off	Yes (Can be enabled or disabled)
Automatic Altitude Adjustment	Up to 9,800 feet
Bluetooth	Bluetooth 2.1 +EDR and Bluetooth 4.0
Chamber warranty	3 months
Dimensions	3.7" (H) x 6.1" (W) x 5.9" (D) - unit only   6.3" (H) x 6.1" (W) x 7.6" (D) with humidifier
Effective Bluetooth Range	50 meters, direct line of sight
Humidifier warranty	3 years
Pressure Range	3-20 cm H <sub>2</sub> O
SmartCode® Feature	Yes
SmartLink® Compatible	Yes
Sound	26.6 dBA
Unit Warranty	3 Years
Weight	1.93 lbs - unit only

  

ACCESSORIES	Description
DV6C	Humidifier Water Chamber Packaged, EA
DV6HHPD	Heated Humidifier W/PD Packaged, EA
DV6HH	Heated Humidifier Packaged, EA
DV6SD-1	IntelliPAP 2 SD card, EA
DV6WM-NA	IntelliPAP 2 Wireless Modem, EA
SL3-USB	SmartLink 3.0 USB, EA
DV6X-619	DC car adaptor for IntelliPAP 2, EA

**ACCESSORIES****Description**

8000AA-WO2	Nonin oximeter adult finger clip sensor, EA
8000J-WO2	Nonin oximeter adult flex sensor, EA
8000SL-WO2	Nonin oximeter soft sensor - Large, EA
8000SM-WO2	Nonin oximeter soft sensor - Medium, EA
8000SS-WO2	Nonin oximeter soft sensor - Small, EA
DV63D-613	65W power supply, EA
DV51D-606	US POWER CORD, EA
DV51D-608	UK POWER CORD, EA
DV51D-607	EUROPE POWER CORD, EA
DV51D-609	AUSTRALIA POWER CORD, EA

**PARTS****Description**

DV51D-602	AIR INLET FILTER, GRAY, 4/pk, EA
DV51D-603	FINE PARTICLE AIR FILTER White, 4/PK, EA
DV61D-604	Air Filter Cover, EA
DV63D-631	Filter Cover for DV63/64, EA
7353D-601	OXYGEN ADAPTER - DFT, EA